

# Multi-Aperture cores (2867002302)

Part Number: 2867002302

67 MULTI-APERTURE CORE

## **Explanation of Part Numbers:**

- Digits 1 & 2 = Product Class
- Digits 3 & 4 = Material Grade
- Last digit 2 = Burnished

Multi-aperture cores are used in suppression applications and in balun (balance-unbalance) and other broadband transformers. They are also employed in airbag designs to prevent accidental activation.

All multi-aperture cores are supplied burnished.


Our "Multi-Aperture Core Kit" (part number 0199000036) is available for prototype evaluation.

For any multi-aperture requirement not listed here, feel free to contact our customer service group for availability and pricing.

Catalog Drawing
3D Model

Weight: 0.1 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	3.45	±0.25	0.136	_
	2.35	±0.25	0.093	_
С	2	±0.15	0.079	_
Е	1.45	±0.10	0.057	_
Н	0.75	+0.25	0.034	_






Figure 1

## **Chart Legend**

+ Test frequency


Electrical	Properties	
$A_L(nH)$	18 Min	

Multi-aperture cores in 73 and 43 materials are controlled for impedance only. The 61 NiZn material is controlled for both impedance and  $A_{\scriptscriptstyle L}$  value. The high frequency 67 material is controlled for  $A_{\scriptscriptstyle L}$  value. Minimum impedance values are specified for the + marked frequencies. The minimum impedance is typically the listed impedance less 20%.

### **Catalog Drawing**

Multi-aperture cores in 73 and 43 material are measured for impedance on the E4990A Impedance Analyzer. The 61 and 67 multi-aperture cores are tested on the E4991A / HP4291B Impedance Analyzer. All impedance measurements are performed with a single turn to both holes, using the shortest practical wire length.

The 61 and 67 material multi-hole beads are tested for  $A_L$  value. The test frequency is 10 kHz at < 10 gauss. The test winding is five turns wound through both holes.



#### **CSV** Download