Fair-Rite Products Corp. Your Signal Solution*



Part Number: 2861002402

67 MULTI-APERTURE CORE

Explanation of Part Numbers:

- Digits 1 & 2 = Product Class
- Digits 3 & 4 = Material Grade
- Last digit 2 = Burnished

Multi-aperture cores are used in suppression applications and in balun (balanceunbalance) and other broadband transformers. They are also employed in airbag designs to prevent accidental activation.

All multi-aperture cores are supplied burnished.

Our "Multi-Aperture Core Kit" (part number 0199000036) is available for prototype evaluation.

For any multi-aperture requirement not listed here, feel free to contact our customer service group for availability and pricing.

Catalog Drawing 3D Model

<u>Weight:</u> 0.5 (g)

Dim	mm	mm tol	nominal inch	inch misc.	
А	7	±0.25	0.276	_	0
В	6.2	±0.25	0.244	_	
С	4.2	-0.25	0.16	_	U
Е	2.9	±0.10	0.114	_	
Η	1.7	+0.20	0.071	_	




Figure 1

Chart Legend

+ Test frequency


Typical Impedance (Ω				
100 MHz	102			
250 MHz	136			
Electrical Properties				
A _L (nH)	160	Min		

Multi-aperture cores in 73 and 43 materials are controlled for impedance only. The 61 NiZn material is controlled for both impedance and A_L value. The high frequency 67 material is controlled for A_L value. Minimum impedance values are specified for the + marked frequencies. The minimum impedance is typically the listed impedance less 20%.

Catalog Drawing

Multi-aperture cores in 73 and 43 material are measured for impedance on the E4990A Impedance Analyzer. The 61 and 67 multi-aperture cores are tested on the E4991A / HP4291B Impedance Analyzer. All impedance measurements are performed with a single turn to both holes, using the shortest practical wire length.

The 61 and 67 material multi-hole beads are tested for A_L value. The test frequency is 10 kHz at < 10 gauss. The test winding is five turns wound through both holes.



CSV Download