

Part Number: 2944777721

44 WOUND BEAD

Explanation of Part Numbers:

- Digits 1 & 2 = Product Class
- Digits 3 & 4 = Material Grade
- Last digit 1 = Bulk Packed 4 = Taped and Reeled

**Six and eleven hole beads, in two NiZn materials, are available both as beads (product class 26) and wound with tinned copper wire in several winding configurations (product class 29).**

Wire used for winding is oxygen free high conductivity copper with 100% matte tin plating over a nickel undercoating.

Recommended storage temperature and operating temperature is -55 °C to 125 °C

[Recommended Soldering Profile](#)

Packaging Options:

- Parts with a 1 as the last digit of the part number are supplied bulk packed. Wound beads with part numbers 29-666631 and 29-666651 can be supplied radially taped and reeled per IEC 60286-1 and EIA 468-B standards. For these taped and reeled wound beads the last digit of the part number is a 4. Taped and reeled wound beads are supplied 500 pieces on a 13 reel.

**For any wound bead requirement not listed in here, please contact our customer service group for availability and pricing.**


[Catalog Drawing](#)

[3D Model](#)

Weight: 3.9 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	10	±0.25	0.394	—
B	0.9	+0.15	0.038	—
C	10	±0.25	0.394	—
D	7.5	Ref	0.295	Ref

Winding Information			
Turns	Wire	1st Wire	2nd Wire
Tests	Size	Length	Length
2 x 2½	0.65 22 AWG	38.0 ±3.0 (1.496")	28.0 ±3.0 (1.102")



### Chart Legend

+ Test frequency

• A ½ turn is defined as a single pass through a hole.



Typical Impedance (Ω)	
1 MHz	86
10 MHz <sup>+</sup>	425
50 MHz <sup>+</sup>	900
100 MHz <sup>+</sup>	985
200 MHz	755

Beads are controlled for impedance limits only. Minimum impedance values are specified for the + marked frequencies. The minimum impedance is typically the listed impedance less 20%.

### [Catalog Drawing](#)

The 44 material beads and wound beads are tested on the E4990A Impedance Meter. The 61 material parts on the E4991A / HP4291B Impedance Analyzer.

Typical Impedance (Ω)	
1 MHz	45
10 MHz <sup>+</sup>	375
50 MHz <sup>+</sup>	905
100 MHz <sup>+</sup>	500
200 MHz	400



[CSV Download](#)

